


Data Sheet

# Chrome plated compression fittings for X-tra Collection™

**Application,  
chrome plated fittings**



Chrome plated compression fittings for design valves DN 15

Danfoss chrome plated compression fittings are only for connection of Danfoss valves to circuits in heating systems.

Compression fittings are used for connecting steel and copper pipes in accordance with DIN EN 10305-1 & DIN EN 1057 as well as for AluPEX and PEX plastic tubings in accordance with DIN 16892/16893.

Maximum operating pressure and temperature are given by the tubing manufacturer. However, the values stated in this data sheet must not be exceeded.

One set consists of one olive and one union nut. Sets for AluPEX and PEX also includes a supporting bush.

**Ordering and technical data**

Connection	Tube dimension	Code no.	Max. work pressure	Test pressure	Max. flow temp.	For:
for steel and copper tubing	10 mm	<b>013G4192</b>	10 bar	16 bar	120 °C	RA-NCX, RA-URX, RLV-CX, VHX, VHS-FX, VHS-RX
	12 mm	<b>013G4193</b>				
	14 mm	<b>013G4194</b>				
	15 mm	<b>013G4195</b>				
	16 mm	<b>013G4196</b>				
for AluPEX tubing	16 x 2 mm	<b>013G4200</b>	6 bar	10 bar	95 °C	
for PEX tubing	12 x 1.1 mm	<b>013G4197</b>	6 bar	10 bar	95 °C	
	15 x 2,5 mm	<b>013G4199</b>				
	16 x 2 mm	<b>013G4198</b>				

## Data Sheet

## Compression fittings in chrome - for X-tra Collection™

**Application,  
nickel plated fittings**

Nickel plated compression fittings (alternative to chrome plated)

Danfoss nickel plated compression fittings are only for connection of Danfoss valves to circuits in heating systems.

Compression fittings are used for connecting steel and copper pipes in accordance with DIN EN 10305-1 & DIN EN 1057 as well as for AluPEX and PEX plastic tubings in accordance with DIN 16892/16893.

Maximum operating pressure and temperature are given by the tubing manufacturer. However, the values stated in this data sheet must not be exceeded.

One set consists of one olive and one union nut. Sets for AluPEX and PEX also includes a supporting bush.

**Ordering**

Connection	Tube dimension	Code no.	Max. work pressure	Test pressure	Max. flow temp.	For:
for steel and copper tubing	8 mm	<b>013G4108</b>	10 bar	16 bar	120 °C	RA-URX, RLV-X, VHX, VHS-FX, VHS-RX, FJVR 15, RA-N 15, RA-UN 15, RLV 15, lance valves
	10 mm	<b>013G4110</b>				
	12 mm	<b>013G4112</b>				
	14 mm	<b>013G4114</b>				
	15 mm	<b>013G4115</b>				
	16 mm	<b>013G4116</b>				
for AluPEX tubing	12 x 2 mm	<b>013G4172</b>	6 bar	10 bar	95 °C	
	14 x 2 mm	<b>013G4174</b>				
	16 x 2 mm	<b>013G4176</b>				
for PEX tubing	12 x 1.1 mm	<b>013G4143</b>	6 bar	10 bar	95 °C	
	12 x 2 mm	<b>013G4142</b>				
	14 x 2 mm	<b>013G4144</b>				
	15 x 2.5 mm	<b>013G4147</b>				
	16 x 2 mm	<b>013G4146</b>				

Danfoss A/S  
Heating Solutions  
Haarupvaenget 11  
8600 Silkeborg  
Denmark  
Phone: +45 7488 8000  
Fax: +45 7488 8100  
e-mail: heating.solutions@danfoss.com  
www.heating.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.